CATHODE RAY TUBE TYPE 21AMP23A

The tube type 21AMP23A is a magnetic focus and magnetic deflection direct view picture tube. It has an all glass rectangular bulb designed for 90° deflection. The faceplate is of gray glass and has a spherical contour. It has an electron gun designed to be used with an ion-trap magnet. It has an external conductive coating. It has a metal-backed screen to increase light output.

GENERAL CHARACTERISTICS

Focusing Method	Magnetic	
Deflection Method	Magnetic	
Deflection Angle (Approx) Horizontal	85	Degrees
Diagonal	90	Degrees
Face Plate Light Transmission	, ,	6
(Neutral Density Filter)	71%	Approx.
(Medicial Deligito) Filter)	(1/0	Appr oxe
Phosphor	No. 23	
Fluorescence	Brown (Sepia)	
Persistence	Medium	
. 02.22.50		
Direct Interelectrode Capacitances (Approx.)		
Cathode to all other electrodes	5	\mathbf{uuf}
Grid No. 1 to all other electrodes		uuf
External Conductive Coating to Anode	750	Max. uuf
Tirage irea action and the action	- · · · · · · · · · · · · · · · · · · ·	Min. uuf
	700	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,
MECHANICAL DATA		
Overall Length	20 ± 7/16	Inches
Greatest Dimensions of Bulb:	·	
Diagonal	$21-3/8 \pm 1/8$	Inches
Width	$20-1/4 \pm 1/8$	
Height	$16-3/8 \pm 1/8$	
Minimum Useful Screen Dimensions	15 x 19-1/8	Inches
Bulb Contact	J1-21	
Base	B5 - 57	
Basing	12N	
Bulb Contact Alignment		
J1-21 Contact Aligns with Pin Position #6	± 30	Degrees
-	•	•

RATINGS Design Center Values

Heater Voltage	-	Volts
Heater Current	0.6 ± 10%	Amperes
Anode Voltage ¹	18,000	Max. Volts D.C.
Grid No. 2 Voltage	500	Max. Volts D.C.
Grid No. 1 Voltage		
Negative Bias Value	125	Max. Volts D.C.
Positive Bias Value	0	Max. Volts D.C.
Positive Peak Value	2	Max. Volts

from JETEC release #1333, July 16, 1954

6-17-54 9-1-21AMP23A

NATIONAL VIDEO CORPORATION

21ANP23A

Peak Heater-Cathode Voltage	
Heater negative with respect to cathode	
during warm-up period not to exceed 15 seconds	410 Max. Volts D.C.
After equipment warm-up	180 Max. Volts D.C.
Heater positive with respect to cathode	180 Max. Volts D.C.

TYPICAL OPERATING CONDITIONS

Anode Voltage	16,000	Volts D.C.
Grid No. 2 Voltage	300	Volts D.C.
Grid No. 1 Voltage ²	-33 to -77	Volts D.C.
Focusing Coil Current ³	102 ± 20%	Ma. D.C.
Ion-Trap Magnet Current4	95 ± 50%	Ma. D.C.

MAXIMUM CIRCUIT VALUES

Grid No. 1 Circuit Resistance

1.5 Max. Megohms


NOTES

Because the rating of the tube permits anode voltages as high as 19.8 kilovolts (absolute maximum), shielding of x-ray radiation from the tube may be necessary. This precaution should be observed when the anode is operated in excess of 16 kilovolts.

²Visual extinction of undeflected, focused spot.

 3 For JETEC standard focus coil #109 with a combined grid 1 bias and video signal voltage adjusted to produce a highlight brightness of 30 foot lamberts on a picture area of 15 x 19-1/8 inches. Distance from reference line of bulb to center of focus coil air gap equal to 3 inches.

4For JETEC #111 single-field ion-trap magnet at optimum position.



NOTES

- NOTE 1: The plane through the tube axis and vacant pin position 6 aligns with the anode contact ± 30°.
- NOTE 2: Reference line is determined by the plane where the standard JETEC reference line gauge #116 will stop against the bulb.
- NOTE 3: Socket for this base should not be rigidly mounted. It should have flexible leads and be free to move.
- NOTE 4: Location of deflection yoke and focusing device must be within this space.
- NOTE 5: Keep this space clear for ion-trap magnet.